


**Approximate dimensions**  
Non-fused, across the line  
Fused, across the line

3



**Non-fused, across the line w/CCT**

Starter size	Enclosure type	A	B	C
A9 – A40	1	10	8	6
	3R	10	8	6
	4	10	8	6
	4X Stainless	10	8	6
	4X Plastic	10	8	7
	12	10	8	6
A50 – A75	1	14	12	8
	3R	14	12	8
	4	14	12	6
	4X Stainless	14	12	6
	4X Plastic	14	12	7
	12	14	12	8
A95 – A110	1	20	16	8
	3R	20	16	8
	4	20	16	8
	4X Stainless	20	16	8
	4X Plastic	20	16	8
	12	20	16	8
A145 – A185	1	30	24	12
	3R	30	20	8
	4	30	20	8
	4X Stainless	30	24	8
	4X Plastic	30	20	12
	12	30	20	8
A210 – A300	1	30	24	12
	3R	30	20	10
	4	30	20	10
	4X Stainless	30	24	12
	4X Plastic	30	20	12
	12	30	20	10
A400	1	36	30	12
	3R	36	30	10
	4	36	30	10
	4X Stainless	36	30	12
	4X Plastic	–	–	–
	12	36	30	10
A460	1	42	30	12
	3R	42	36	12
	4	42	36	12
	4X Stainless	42	36	12
	4X Plastic	–	–	–
	12	42	36	12
A580	1	36	30	12
	3R	36	30	10
	4	36	30	10
	4X Stainless	36	30	12
	4X Plastic	–	–	–
	12	36	30	10
A750	1	–	–	–
	3R	60	36	16
	4	60	36	16
	4X Stainless	60	36	16
	4X Plastic	–	–	–
	12	60	36	16

**Fused, across the line w/CCT**

Starter size	Enclosure type	A	B	C
A9 – A40	1	14	12	8
	3R	14	12	8
	4	14	12	6
	4X Stainless	14	12	6
	4X Plastic	14	12	7
	12	14	12	8
A50 – A75	1	20	16	8
	3R	20	16	8
	4	20	16	8
	4X Stainless	20	16	8
	4X Plastic	20	16	8
	12	20	16	8
A95 – A110	1	24	20	10
	3R	24	20	10
	4	24	20	10
	4X Stainless	24	20	10
	4X Plastic	24	20	12
	12	24	20	10
A145 – A185	1	30	24	12
	3R	30	20	10
	4	30	20	10
	4X Stainless	30	24	12
	4X Plastic	30	20	12
	12	30	20	10
A210 – A400	1	36	30	12
	3R	30	30	10
	4	30	30	10
	4X Stainless	36	30	12
	4X Plastic	40	30	14
	12	30	30	10
A460	1	42	30	12
	3R	42	36	12
	4	42	36	12
	4X Stainless	42	36	12
	4X Plastic	–	–	–
	12	42	36	12
A580 – A750	1	87	36	24
	3R	87	36	24
	4	87	36	24
	4X Stainless	–	–	–
	4X Plastic	–	–	–
	12	87	36	24